


## BeaconMedaes Floor Mounted Stainless Steel Service Pedestal

### SPECIFICATION


#### Service Pedestal

Where indicated on the mechanical drawing, provide a **BeaconMedaes** floor mounted service pedestal with (8 or 12) factory installed gas and electrical services. Service pedestal shall be made of 16-gauge, number 3 brushed finish 304 stainless steel and have overall physical dimensions of 20" W x 10" D x 16" H. The top panel shall be stainless steel and removable to provide quick access for service. The pedestal shall have four mounting holes for installation. Blank trim plates shall be provided in all unused locations for the future installation of medical gas or electrical services. All welds shall be ground smooth. Medical gas rough-ins shall be factory installed. Each medical gas rough-in shall terminate in an 8" length of type-K copper tubing for final connection to the medical gas distribution system by the installer. Medical gas outlet latch valves and cover plates shall be packaged with the service pedestal for installation into the unit. Outlets shall be Diameter-Index Safety System (DISS), Puritan Bennett, Chemetron® type, or Medaes® type quick-connect as specified on the gas service and accessory selection chart located on the back. Outlets shall be UL listed, CSA approved, and meet NFPA 99 and CSA Z305.1 standards. All outlets shall be tested and cleaned for oxygen service prior to shipping. The electrical contractor shall provide electrical wiring to pre-installed electrical rough-in boxes. Electrical receptacles and cover plates shall be packaged with the service pedestal for installation into the unit as indicated on the selection chart. The service pedestal installation location may vary according to specific conditions or preference.



**Note:**  
 Services may be other than shown above.  
 Pedestal services to be per customer specifications shown on reverse side of this sheet.

### PART NUMBERING SCHEME



Service Pedestal	
Item	Part Number
<b>Basic Shell 20" x 10" x 16"*</b> (0-8 service options, A-H)	<b>6-PED08 - ____</b>
<b>Basic Shell 20" x 10" x 16"</b> (0-12 service options, A-L)	<b>6-PED12 - ____</b>

**\*NOTE:** P/N 6-PED08-XX has a solid back panel. No future expansion in positions "P", "J", "K", or "L" as shown in the layout on page 2.

### BeaconMedaes Floor Mounted Stainless Steel Service Pedestal


Service Pedestals are manufactured to customer specifications. The drawings below indicate the possible locations of services. Select the services desired and fill in the appropriate position letter (A through L) in the selection charts. Multiple locations for a particular service may be selected.

**NOTE: BeaconMedaes requires a signed, approved copy of this specification before fabrication will begin.**

Number of Pedestals \_\_\_\_\_

Project Name \_\_\_\_\_

Approved by \_\_\_\_\_ Date \_\_\_\_\_



**\*NOTE: P/N 6-PED08-XX has a solid back panel. No future expansion in positions "I", "J", "K", or "L".**

	OUTLET TYPE				**SERVICE LOCATION (S) Indicate location(s) with letter	QUANTITY
	PURTAN BENNETT Quick Connect	MEDAES® Type Quick Connect	Chemtron® Type Quick Connect	DISS		
<b>GAS SERVICE</b>						
Oxygen						
Nitrous Oxide						
Air						
Vacuum						
WAGD						
Nitrogen	NOT AVAILABLE					
Carbon Dioxide						
CO2-O2 CO2 Over 7%						
O2-CO2 CO2 Not Over 7%						
Vacuum Slide Bracket						
ISO	Oxygen					
	Air					
	Vacuum					

ELECTRICAL SERVICE	OPTIONS	**SERVICE LOCATION (S) Indicate location(s) with letter	QUANTITY
HUBBELLOCK® Receptacle			
Duplex Power Receptacle 125V, 15 AMP (Circle One Color)	Red		
	Gray		
	Ivory		
Duplex Power Receptacle 125V, 20 AMP (Circle One Color)	Red		
	Gray		
	Ivory		
Grounding Receptacle			
Future Electrical Provision			
<b>TOTAL Selected Services (Gas + Electrical)</b>			<b>XX</b>

**\*\* Note: Blank cover plates are supplied for locations without a specified service.**