


DESICCANT AIR DRYER SOLENOID VALVE ASM  
(LOCATED ON SIDE OF CONTROL PANEL LEG)



INSTRUMENTATION DETAILS			
SENSOR	DESCRIPTION	SETTING	ACTION
S1	HIGH DISCH TEMP	5HP-465°F	SHUTDOWN
S2	PRESS TRANSDUCER	7.5HP-465°F 0-145PSI	OPERATION
S3	BACKUP PRESS SW.	CUT IN-110PSI CUT OUT-135PSI	BACKUP OPERATION
S4	DP SENSOR	-30° C	ALARM

Revised: SMB	Date: 11/19/2019	Drawn: SMB	Date: 08/12/2019
		This drawing and the information contained thereon remain the property of BeaconMedics and may not be used for other than the purpose for which it is loaned without the expressed written permission from BeaconMedics Engineering.	
Description: DWG PNEU QX SCRL LAB 5-7.5HP 10BAR -40		Part Number: 4107 8570 30	
DNE: HOP191299		Scale: NTS	
Sheet 1 of 1		DO NOT SCALE THIS DOCUMENT	